TWIN-PAK 20


INSTALLATION INSTRUCTIONS

Installation Procedure:

- From job schedule or plan, determine proper assemblies for each wall.
- Install partial backplate at proper height and level (Note: Where valve compartments occur, allow 12" for partial backplate).
- 3. Bracket Installation: Insert carriage bolt through pitch adjustment slot in bracket assembly. Locate bracket assembly with partial backplate and screw to wall (Note: 2 bracket assemblies for enclosures 3' thru 6', and 3 for 7' and 8'). Install hanger assembly with serrated flange nut and carriage bolt.
- 4. Install wall sleeve supports, if any.
- 5. Lay element on floor (Note: 4 1/4 fin dimension to be horizontal). Place cradles on element and position them so that the center of the cradles will rest on the ball bearings of the hanger assemblies. Install element with cradles on hanger assemblies.
- 6. Install enclosure. Begin with lower enclosure. Insert the lower enclosure top bend into the armature bracket, then swing lower enclosure bottom into position with enclosure lock and tighten. Place upper enclosure top bend into partial backplate, then swing upper enclosure bottom to the armature bracket and push into place.
- 7. Install accessories. Accessories are the overlapping type with a bottom return to the wall. Push the top bend of the accessories down behind the partial backplate and anchor the return to the wall bend at bottom for a sturdy installation.

- 1 ELEMENT
- 2 UPPER ENCLOSURE
- (3) LOWER ENCLOSURE
- (4) FASTENERS BY OTHERS
- 5 CRADLE


- (6) BRACKET ASSEMBLY
- 7 PARTIAL BACKPLATE
- 8 HANGER ASSEMBLY
- 9 CARRIAGE BOLT
- (10) SERRATED FLANGE NUT




TP-20



260 North Elm Street • Westfield, MA 01085 Tel: (413) 562-5423 • Fax: (413) 572-3764 www.beacon-morris.com



ELEMENT CATALOG DESIGNATION	NOMINAL PIPE SIZE	CRADLE NO.	A MIN	A MAX
STC-3/4 435	3/4 COPPER	2	7 3/8	8 1/2
STC-435	1" COPPER	2	7 1/2	8 5/8
STC-1435	1 1/4 COPPER	2	7 5/8	8 13/16
ST-144	1 1/4 STEEL	2	7 7/8	8 15/16
ST-243	2" STEEL	1	7 5/8	8 3/4



STANDARD LENGTHS: AVAILABLE FROM 3' THRU 8' IN 12" INCREMENTS